

# Warm Tiles™ ESW WiFi ColorTouch Thermostat

Floor Warming. For Residential and Commercial Applications.

## Product Overview

- The Warm Tiles™ ESW Wifi ColorTouch Thermostat allows monitoring and precise control of Warm Tiles floor warming systems remotely from a web browser, Android or iOS smartphone or tablet. It offers all the same features of the ES Thermostat with the addition of wifi capability for remote access.

## Applications

- Monitors and controls Warm Tiles floor warming systems remotely via a user-friendly app or laptop pc.

## Features

- 3.5" color screen with easy interactive touch control.
- Programmable thermostat allowing for 6 programming periods per day.
- Integral relay switch can control up to 15 amps at either 115 Vac or 230 Vac.
- Includes 5 mA built-in ground fault circuit interrupter (GFCI) with indicator light.
- WLAN connectivity for remote access.
- Connects to standard home wifi- No hub required.
- Monitor and precisely control any Warm Tiles floor warming system from a web browser, Android™ or iOS™ smartphone or tablet.
- Compatible with iPhone™ and iPad™ devices using iOS™ operating system.
- Compatible Samsung™ and Motorola™ devices using Android™ operating systems.
- Local weather information can be displayed on the thermostat with just a tap of the screen.
- Black back-lit screen with white characters proves high contrast for easy readability from a distance and in bright or dark environments.
- Track thermostat power consumption in the energy log.
- Lockout feature prevents others from tampering with thermostat settings.
- 5-year battery back-up included.
- 3 year plus 3 month warranty.



## Certifications

- UL Listed for use in the United States and Canada.

### Notes

- Thermostats are designed for indoor use only and should not be installed in areas where it can be exposed to water or rain.

## Product Selection

Catalog Number	Description	Dimensions in (mm)	Carton Quantity	Carton Weight lb (kg)	UPC
ESW	WiFi-enabled Color Touch-Screen Thermostat 120/240V, 15A	3.5x6 (89x152)	1	1 (0.3)	013627-00298-2